






4 Type

- A** with cylinder head screw
DIN 912
- B** with countersunk screw
DIN 7991
- C** with lens screw ISO 7380
- D** with cylinder head screw
DIN 7984



b	n	d	I ₁				k ≈ Clamping length	I ₂	I ₃	s ≈	t ≈
			Type A	Type B	Type C	Type D					
30	6	M 4	10	-	-	-	... 4	5	12	2,9	8,9
30	6	M 4	12	-	-	-	1 ... 6	5	12	2,9	8,9
30	6	M 4	16	-	-	-	5 ... 10	5	12	2,9	8,9
30	6	M 5	10	-	-	-	... 3	5	12	2,9	8,9
30	6	M 5	12	12	-	-	1 ... 5	5	12	2,9	8,9
30	6	M 5	14	-	-	-	3 ... 7	5	12	2,9	8,9
30	6	M 5	16	-	-	-	5 ... 9	5	12	2,9	8,9
30	6	M 5	18	-	-	-	7 ... 11	5	12	2,9	8,9
30	6	M 5	22	-	-	-	11 ... 15	5	12	2,9	8,9
30	6	M 6	-	-	-	10	... 3	5	12	2,9	8,9
30	6	M 6	12	12	-	-	1 ... 4	5	12	2,9	8,9
30	6	M 6	14	-	14	-	3 ... 6	5	12	2,9	8,9
30	6	M 6	16	16	-	-	5 ... 8	5	12	2,9	8,9
30	6	M 6	-	18	-	-	7 ... 10	5	12	2,9	8,9
30	6	M 6	20	-	-	-	9 ... 12	5	12	2,9	8,9
30	6	M 6	25	-	-	-	14 ... 17	5	12	2,9	8,9
40	8	M 4	12	-	-	-	... 5	7	15	4,6	11,4
40	8	M 4	14	-	-	-	1 ... 7	7	15	4,6	11,4
40	8	M 4	20	-	-	-	7 ... 13	7	15	4,6	11,4
40	8	M 5	12	-	-	-	... 4	7	15	4,6	11,4
40	8	M 5	14	14	-	-	1 ... 6	7	15	4,6	11,4
40	8	M 5	16	-	-	-	3 ... 8	7	15	4,6	11,4
40	8	M 5	18	-	-	-	5 ... 10	7	15	4,6	11,4
40	8	M 5	20	-	-	-	7 ... 12	7	15	4,6	11,4
40	8	M 5	22	-	-	-	9 ... 14	7	15	4,6	11,4
40	8	M 5	25	-	-	-	12 ... 17	7	15	4,6	11,4
40	8	M 6	14	14	-	14	1 ... 5	7	15	4,6	11,4
40	8	M 6	16	16	16	-	3 ... 7	7	15	4,6	11,4
40	8	M 6	18	18	-	-	5 ... 9	7	15	4,6	11,4
40	8	M 6	-	20	-	-	7 ... 11	7	15	4,6	11,4
40	8	M 6	22	-	22	-	9 ... 13	7	15	4,6	11,4
40	8	M 6	28	-	-	-	15 ... 19	7	15	4,6	11,4
40	8	M 8	14	-	-	-	1 ... 4	7	15	4,6	11,4
40	8	M 8	16	16	16	-	3 ... 6	7	15	4,6	11,4
40	8	M 8	18	-	18	-	5 ... 8	7	15	4,6	11,4
40	8	M 8	20	-	-	-	7 ... 10	7	15	4,6	11,4
40	8	M 8	28	-	-	-	15 ... 18	7	15	4,6	11,4

Specification

- T-Nuts GN 506
Steel
- zinc plated, blue passivated
- Ball / Spring
Stainless Steel
- Cylinder head screws DIN 912
Counter sunk screws DIN 7991
Lens head screws ISO 7380
Cylinder head screws DIN 7984
Steel
zinc plated, blue passivated
- RoHS compliant

Information

Assembly sets GN 965 allow different standard element to be attached to the most common profile systems. Each set includes one T-nut GN 506 and one screw.

GN standards with assembly sets for profile systems → Page 10 ff.



see also...



- T-Nuts GN 506 → Page 27



How to order



GN965-8-M6-18-B



1 n
2 d
3 I₁
4 Type




Assembly sets GN 965		Type A	Type B	Type C	Type D
					
Compatible GN standards in ascending order of the standard numbers					
Hinges GN 127 → Page 49					
	GN 127-...-B	-		GN 965-8-M6-20-B	
Mounting plate GN 139.3 (for hinges with / without safety switch GN 139.1 / GN 139.2) → Page 62					
	GN 139.3-170	GN 965-6-M6-12-A		GN 965-8-M6-14-A	
Mounting plate GN 139.4 (for hinges with / without safety switch GN 139.1 / GN 139.2) → Page 62					
	GN 139.4-101	GN 965-6-M6-12-A		GN 965-8-M6-14-A	
Flanged connector clamps GN 145 → Page 63					
	GN 145-...	-		GN 965-8-M5-16-A	
Hinges GN 151.4 → Page 51					
	GN 151.4-...	-		GN 965-8-M6-18-A	
Hinges GN 159 → Page 52					
	GN 159-54-17,5-17,5 GN 159-74-22,5-22,5	GN 965-6-M6-16-B -		- GN 965-8-M6-18-B	
Double hinges GN 159.1 → Page 54					
	GN 159.1-89-35-35 GN 159.1-119-45-45	GN 965-6-M6-16-B -		- GN 965-8-M6-18-B	


Assembly sets GN 965		Type A	Type B	Type C	Type D
					
Compatible GN standards in ascending order of the standard numbers					
Hinges GN 161 → Page 60					
	GN 161-57 / 68 / 80	-		GN 965-8-M6-16-B	
Base plate connector clamps GN 162.3 → Page 67					
	GN 162.3-...	GN 965-6-M5-16-A		GN 965-8-M5-18-A	
Tube supports GN 231 → Page 64					
	GN 231-B20 / B25 / B30 GN 231-V20 / V25 / V30	-		GN 965-8-M8-14-A GN 965-8-M8-14-A	
Hinge GN 236 → Page 50					
	GN 236-75-60	-		GN 965-8-M6-20-B	
Hinge GN 239.3 → Page 56					
	GN 239.3-70-60-SH	-		GN 965-8-M6-18-B	
Hinges with switch GN 239.4 → Page 56					
	GN 239.4-...	-		GN 965-8-M6-18-B	
Hinges with safety switch GN 239.6 → Page 58					
	GN 239.6-60-110-...	-		GN 965-8-M6-18-B	

Assembly sets GN 965		Type A	Type B	Type C	Type D
					
Compatible GN standards in ascending order of the standard numbers					
Hinges GN 239.7 → Page 58					
	GN 239.7-60-70 GN 239.7-60-110			-	GN 965-8-M6-18-B
Swivel clamp connector bases GN 271 → Page 65					
	GN 271-25-...			-	GN 965-8-M5-18-A
Swivel clamp connector joints GN 281 → Page 66					
	GN 281-...			-	GN 965-8-M5-18-A
Tubular handles GN 333 → Page 38					
	GN 333-28-...-B-...	GN 965-6-M6-25-A		GN 965-8-M6-28-A	
Tubular handles GN 333.1 → Page 36					
	GN 333.1-28-...-B-...	GN 965-6-M6-14-C		GN 965-8-M6-16-C	
Oval tubular handles GN 334.1 → Page 40					
	GN 334.1-36-...			-	GN 965-8-M8-16-C
Mounting blocks GN 412.1 → Page 43					
	GN 412.1-35-... GN 412.1-47-...	GN 965-6-M4-16-A GN 965-6-M5-18-A		- GN 965-8-M5-20-A	

Assembly sets GN 965		Type A	Type B	Type C	Type D
					
Compatible GN standards in ascending order of the standard numbers					
Indexing plungers GN 417 → Page 44 / 45					
	GN 417-5-A / -B / -C GN 417-6-A / -B / -C GN 417-8-A / -B GN 417-8-C	GN 965-6-M4-12-A GN 965-6-M5-14-A GN 965-6-M5-14-A -	- GN 965-8-M5-16-A GN 965-8-M5-16-A GN 965-8-M5-16-A		
Base clamp mountings GN 473 → Page 68					
	GN 473-B8-... GN 473-B10 / B12-... GN 473-B15 / B16-... GN 473-B20-...	GN 965-6-M4-10-A - - -	GN 965-8-M4-14-A GN 965-8-M5-12-A GN 965-8-M6-14-A GN 965-8-M6-18-A		
Clamp mountings GN 477 → Page 69					
	GN 477-B8-... GN 477-B10 / B12-... GN 477-B15 / B16 / B20-...	GN 965-6-M4-16-A GN 965-6-M5-18-A GN 965-6-M6-20-A	GN 965-8-M4-20-A GN 965-8-M5-20-A GN 965-8-M6-22-A		
Flanged bolts GN 480 → Page 70					
	GN 480-8-... GN 480-10 / 12-... GN 480-15 / 16 / 20-...	GN 965-6-M4-10-A GN 965-6-M5-10-A GN 965-6-M6-12-A	GN 965-8-M4-12-A GN 965-8-M5-12-A GN 965-8-M6-14-A		
Cabinet U-Handles GN 528 → Page 32					
	GN 528-...-94-6,5-... GN 528-...-117-6,5-... GN 528-...-117-8,5-... GN 528-...-132-8,5-... GN 528-...-140-8,5-... GN 528-...-160-8,5-... GN 528-...-179-8,5-...	GN 965-6-M6-14-A GN 965-6-M6-16-A - - - - -	GN 965-8-M6-16-A GN 965-8-M6-16-A GN 965-8-M8-18-A GN 965-8-M8-18-A GN 965-8-M8-18-A GN 965-8-M8-20-A GN 965-8-M8-20-A		
Angle connector brackets GN 561 → Page 73					
	GN 561-19-... GN 561-25-...	- -	GN 965-8-M8-18-C GN 965-8-M8-18-C		

Assembly sets GN 965		Type A	Type B	Type C	Type D
					
Compatible GN standards in ascending order of the standard numbers					
Cabinet U-Handles GN 565.1 → Page 30					
	GN 565.1-20-... GN 565.1-26-...	GN 965-6-M5-22-A -	- GN 965-8-M6-22-A		
Inclined cabinet U-Handles GN 565.2 → Page 31					
	GN 565.2-26-128-B-... GN 565.2-26-160-B-...	- -	GN 965-8-M6-22-C GN 965-8-M6-22-C		
Cam action indexing plungers GN 612.2 → Page 46					
	GN 612.2-...-16-... GN 612.2-...-20-...	GN 965-6-M5-18-A GN 965-6-M5-22-A	GN 965-8-M5-22-A GN 965-8-M5-25-A		
Cam action indexing plungers GN 612.9 → Page 47					
	GN 612.9-...-16-... GN 612.9-...-20-...	GN 965-6-M5-18-A GN 965-6-M5-22-A	GN 965-8-M5-20-A GN 965-8-M5-25-A		
Cabinet U-Handles GN 628 → Page 34					
	GN 628-...-117-6,5-B-... GN 628-...-117-8,5-B-... GN 628-...-150-8,5-B-... GN 628-...-179-8,5-B-...	GN 965-6-M6-16-A - - -	- GN 965-8-M8-28-A GN 965-8-M8-28-A GN 965-8-M8-28-A		
Ledge handles GN 630 → Page 42					
	GN 630-114-B-...	GN 965-6-M6-18-B	GN 965-8-M6-22-C		
Cabinet U-Handles GN 630.1 → Page 41					
	GN 630.1-114-B-...	GN 965-6-M6-18-B	GN 965-8-M6-22-C		

Assembly sets GN 965		Type A	Type B	Type C	Type D
					
Compatible GN standards in ascending order of the standard numbers					
Panel support clamp GN 649 → Page 75					
	GN 649-35-E	GN 965-6-M6-10-D		GN 965-8-M6-14-D	
Cabinet U-Handles GN 667 → Page 75					
	GN 667-20-...	-		GN 965-8-M8-20-A	
Cam action indexing plungers GN 722.3 → Page 48					
	GN 722.3-8-... GN 722.3-10-... GN 722.3-12-... GN 722.3-14-...	- - - -		GN 965-8-M6-18-A GN 965-8-M6-18-A GN 965-8-M6-18-A GN 965-8-M6-18-A	
Cabinet U-Handles GN 728 → Page 33					
	GN 728-120-B-... GN 728-180-B-...	GN 965-6-M6-14-A -		- GN 965-8-M8-18-A	
Angle pieces / Shackles GN 967 → Page 74					
	GN 967-...-20-...-1-... GN 967-...-20-...-2-... GN 967-...-30-...-1-... GN 967-...-30-...-2-... GN 967-...-40-...-1-... GN 967-...-40-...-2-... GN 967-...-45-...-1-... GN 967-...-45-...-2-...	GN 965-6-M5-12-A GN 965-6-M5-12-B GN 965-6-M6-12-A GN 965-6-M6-12-B - - - -		GN 965-8-M5-14-A GN 965-8-M5-14-B GN 965-8-M6-14-A GN 965-8-M6-14-B GN 965-8-M8-16-A GN 965-8-M8-16-B GN 965-8-M8-16-A GN 965-8-M8-16-B	



4 Type

- A** with cylinder head screw
DIN 912
- B** with countersunk screw
DIN 7991
- C** with lens screw ISO 7380
- D** with cylinder head screw
DIN 7984



b	n	d	1 2 3				k ≈ Clamping length	l₂ ±0,5	s ≈	t ≈
			l₁ Type A	Type B	Type C	Type D				
30	8	M 4	10	-	-	-	... 6	16	2,2	7,2
30	8	M 4	12	-	-	-	2 ... 8	16	2,2	7,2
30	8	M 4	16	-	-	-	6 ... 12	16	2,2	7,2
30	8	M 5	10	-	-	-	... 5	16	2,2	7,2
30	8	M 5	12	12	-	-	2 ... 7	16	2,2	7,2
30	8	M 5	14	-	-	-	4 ... 9	16	2,2	7,2
30	8	M 5	18	-	-	-	8 ... 13	16	2,2	7,2
30	8	M 5	20	-	-	-	10 ... 15	16	2,2	7,2
30	8	M 5	22	-	-	-	12 ... 17	16	2,2	7,2
30	8	M 6	10	-	-	10	... 4	16	2,2	7,2
30	8	M 6	12	12	-	-	2 ... 6	16	2,2	7,2
30	8	M 6	14	14	14	-	4 ... 8	16	2,2	7,2
30	8	M 6	16	16	-	-	6 ... 10	16	2,2	7,2
30	8	M 6	-	18	-	-	8 ... 12	16	2,2	7,2
30	8	M 6	20	-	-	-	10 ... 14	16	2,2	7,2
30	8	M 6	25	-	-	-	15 ... 19	16	2,2	7,2
40 / 45	10	M 4	14	-	-	-	... 8	19	6	11,8
40 / 45	10	M 5	12	-	-	-	... 5	19	6	11,8
40 / 45	10	M 5	14	14	-	-	... 7	19	6	11,8
40 / 45	10	M 5	16	-	-	-	3 ... 9	19	6	11,8
40 / 45	10	M 5	18	-	-	-	5 ... 11	19	6	11,8
40 / 45	10	M 5	20	-	-	-	7 ... 13	19	6	11,8
40 / 45	10	M 5	25	-	-	-	12 ... 18	19	6	11,8
40 / 45	10	M 6	14	14	-	14	... 6	19	6	11,8
40 / 45	10	M 6	16	-	-	-	3 ... 8	19	6	11,8
40 / 45	10	M 6	18	18	18	-	5 ... 10	19	6	11,8
40 / 45	10	M 6	20	20	-	-	7 ... 12	19	6	11,8
40 / 45	10	M 6	22	22	22	-	9 ... 14	19	6	11,8
40 / 45	10	M 6	28	-	-	-	15 ... 20	19	6	11,8
40 / 45	10	M 8	14	-	-	-	... 5	19	6	11,8
40 / 45	10	M 8	16	16	16	-	3 ... 7	19	6	11,8
40 / 45	10	M 8	18	-	18	-	5 ... 9	19	6	11,8
40 / 45	10	M 8	20	-	-	-	7 ... 11	19	6	11,8
40 / 45	10	M 8	28	-	-	-	15 ... 19	19	6	11,8

Specification

- T-Nut GN 505
with increased torque (Type MB)
Steel
zinc plated, blue passivated
- Cylinder head screws DIN 912
Counter sunk screws DIN 7991
Lens head screws ISO 7380
Cylinder head screws DIN 7984
Steel
zinc plated, blue passivated
- RoHS compliant

Information

Assembly sets GN 968 allow different standard element to be attached to the most common profile systems. Each set includes one T-nut GN 505 and one screw.

GN standards with assembly sets for profile systems → *Page 18 ff.*

see also...

- T-Nuts GN 505 → *Page 25*

How to order

1



2

3



4

GN968-8-M5-18-A



1	n
2	d
3	l₁
4	Type

Assembly sets GN 968		Type A	Type B	Type C	Type D
					
Compatible GN standards in ascending order of the standard numbers					
Hinges GN 127 → Page 49					
	GN 127-...-B	-	GN 968-10-M6-20-B ¹⁾		
Mounting plate GN 139.3 (for hinges with / without safety switch GN 139.1 / GN 139.2) → Page 62					
	GN 139.3-170	GN 968-8-M6-10-A	GN 968-10-M6-14-A		
Mounting plate GN 139.4 (for hinges with / without safety switch GN 139.1 / GN 139.2) → Page 62					
	GN 139.4-101	GN 968-8-M6-10-A	GN 968-10-M6-14-A		
Flanged connector clamps GN 145 → Page 63					
	GN 145-...	-	GN 968-10-M5-18-A		
Hinges GN 151.4 → Page 51					
	GN 151.4-...-B	-	GN 968-10-M6-18-A ¹⁾		
Hinges GN 159 → Page 52					
	GN 159-54-17,5-17,5 GN 159-74-22,5-22,5 GN 159-84-25-25	GN 968-8-M6-16-B - -	- GN 968-10-M6-18-B ¹⁾ GN 968-10-M6-18-B ²⁾		
Double hinges GN 159.1 → Page 54					
	GN 159.1-89-35-35 GN 159.1-119-45-45 GN 159.1-134-50-50	GN 968-8-M6-16-B - -	- GN 968-10-M6-18-B ¹⁾ GN 968-10-M6-18-B ²⁾		



¹⁾ only for profile 40 x 40 ²⁾ only for profile 45 x 45



Assembly sets GN 968		Type A	Type B	Type C	Type D
Compatible GN standards in ascending order of the standard numbers					
Hinges GN 161 → Page 60					
	GN 161-57 / 68 / 80	GN 968-8-M6-14-B		GN 968-10-M6-18-B	
Base plate connector clamps GN 162.3 → Page 67					
	GN 162.3-...	GN 968-8-M5-14-A		GN 968-10-M5-18-A	
Tube supports GN 231 → Page 64					
	GN 231-B20 / B25 / B30 GN 231-V20 / V25 / V30	-		GN 968-10-M8-14-A GN 968-10-M8-14-A	
Hinge GN 236 → Page 50					
	GN 236-75-60	-		GN 968-10-M6-20-B ¹⁾	
Hinge GN 239.3 → Page 56					
	GN 239.3-70-60-SH	-		GN 968-10-M6-18-B ¹⁾	
Hinges with switch GN 239.4 → Page 56					
	GN 239.4-...	-		GN 968-10-M6-18-B ¹⁾	
Hinges with safety switch GN 239.6 → Page 58					
	GN 239.6-60-110-...	-		GN 968-10-M6-18-B ¹⁾	




¹⁾ only for profile 40 x 40

Assembly sets GN 968		Type A	Type B	Type C	Type D
					
Compatible GN standards in ascending order of the standard numbers					
Hinges GN 239.7 → Page 58					
	GN 239.7-60-70 GN 239.7-60-110	-		GN 968-10-M6-18-B ¹⁾	
Swivel clamp connector bases GN 271 → Page 65					
	GN 271-25-...	-		GN 968-10-M5-18-A	
Swivel clamp connector joints GN 281 → Page 66					
	GN 281-...	-		GN 968-10-M5-18-A	
Tubular handles GN 333 → Page 38					
	GN 333-28-...-B-...	GN 968-8-M6-25-A		GN 968-10-M6-28-A	
Tubular handles GN 333.1 → Page 36					
	GN 333.1-28-...-B-...	GN 968-8-M6-14-C		GN 968-10-M6-18-C	
Oval tubular handles GN 334.1 → Page 40					
	GN 334.1-36-...	-		GN 968-10-M8-16-C	
Mounting blocks GN 412.1 → Page 43					
	GN 412.1-47-...	GN 968-8-M5-18-A		-	

¹⁾ only for profile 40 x 40

Assembly sets GN 968		Type A	Type B	Type C	Type D
					
Compatible GN standards in ascending order of the standard numbers					
Indexing plungers GN 417 → Page 44 / 45					
	GN 417-5-A / -B GN 417-6-A / -B / -C GN 417-8-A / -B	GN 968-8-M4-12-A GN 968-8-M5-14-A GN 968-8-M5-14-A	- GN 968-10-M5-16-A GN 968-10-M5-16-A		
Base clamp mountings GN 473 → Page 68					
	GN 473-B8-... GN 473-B10 / B12-... GN 473-B15 / B16-... GN 473-B20-...	GN 968-8-M4-10-A - - -	GN 968-10-M4-14-A GN 968-10-M5-14-A GN 968-10-M6-14-A GN 968-10-M6-18-A		
Clamp mountings GN 477 → Page 69					
	GN 477-B8-... GN 477-B10 / B12-... GN 477-B15 / B16 / B20-...	GN 968-8-M4-16-A GN 968-8-M5-18-A GN 968-8-M6-20-A	- GN 968-10-M5-20-A GN 968-10-M6-22-A		
Flange bolts GN 480 → Page 70					
	GN 480-8-... GN 480-10 / 12-... GN 480-15 / 16 / 20-...	GN 968-8-M4-10-A GN 968-8-M5-10-A GN 968-8-M6-12-A	- GN 968-10-M5-12-A GN 968-10-M6-14-A		
Cabinet U-Handles GN 528 → Page 32					
	GN 528-...-94-6,5-... GN 528-...-117-6,5-... GN 528-...-117-8,5-... GN 528-...-122-8,5-... GN 528-...-132-8,5-... GN 528-...-140-8,5-... GN 528-...-160-8,5-... GN 528-...-179-8,5-... GN 528-...-235-8,5-...	GN 968-8-M6-14-A GN 968-8-M6-16-A - - - - - - -	GN 968-10-M6-16-A GN 968-10-M6-20-A GN 968-10-M8-16-A GN 968-10-M8-16-A GN 968-10-M8-18-A GN 968-10-M8-18-A GN 968-10-M8-20-A GN 968-10-M8-20-A GN 968-10-M8-20-A		
Angle connector brackets GN 561 → Page 73					
	GN 561-19-...-A / -B / -C GN 561-25-...-A / -B / -C GN 561-43-43-A-...	GN 968-8-M6-14-C GN 968-8-M6-14-C -	- - GN 968-10-M8-18-C		

Assembly sets GN 968		Type A	Type B	Type C	Type D
					
Compatible GN standards in ascending order of the standard numbers					
Cabinet U-Handles GN 565.1 → Page 30					
	GN 565.1-20-... GN 565.1-26-...	GN 968-8-M5-20-A -	GN 968-10-M6-22-A		
Inclined cabinet U-Handles GN 565.2 → Page 31					
	GN 565.2-26-128-B-... GN 565.2-26-160-B-...	- -	GN 968-10-M6-22-C GN 968-10-M6-22-C		
Cam action indexing plungers GN 612.2 → Page 46					
	GN 612.2-...-16-... GN 612.2-...-20-...	GN 968-8-M5-18-A GN 968-8-M5-22-A	GN 968-10-M5-25-A		
Cam action indexing plungers GN 612.9 → Page 47					
	GN 612.9-...-16-... GN 612.9-...-20-...	GN 968-8-M5-18-A GN 968-8-M5-22-A	GN 968-10-M5-25-A		
Cabinet U-Handles GN 628 → Page 34					
	GN 628-...-117-6,5-B-... GN 628-...-117-8,5-B-... GN 628-...-150-8,5-B-... GN 628-...-179-8,5-B-...	GN 968-8-M6-14-A - - -	GN 968-10-M8-28-A GN 968-10-M8-28-A GN 968-10-M8-28-A		
Ledge handles GN 630 → Page 42					
	GN 630-114-B-...	GN 968-8-M6-18-B	GN 968-10-M6-22-B		
Cabinet U-Handles GN 630.1 → Page 41					
	GN 630.1-114-B-...	GN 968-8-M6-18-B	GN 968-10-M6-22-B		

Assembly sets GN 968		Type A	Type B	Type C	Type D
					
Compatible GN standards in ascending order of the standard numbers					
Panel support clamp GN 649 → Page 75					
	GN 649-35-E	GN 968-8-M6-10-D		GN 968-10-M6-14-D	
Cabinet U-Handles GN 667 → Page 35					
	GN 667-20-...	-		GN 968-10-M8-20-A	
Cam action indexing plungers GN 722.3 → Page 48					
	GN 722.3-8-... GN 722.3-10-... GN 722.3-12-... GN 722.3-14-...	- - - -		GN 968-10-M6-18-A GN 968-10-M6-18-A GN 968-10-M6-18-A GN 968-10-M6-18-A	
Cabinet U-Handles GN 728 → Page 33					
	GN 728-120-B-... GN 728-180-B-...	GN 968-8-M6-14-A -		- GN 968-10-M8-18-A	
Angle pieces / Shackles GN 967 → Page 74					
	GN 967-...-20-...-1-... GN 967-...-20-...-2-... GN 967-...-30-...-1-... GN 967-...-30-...-2-... GN 967-...-40-...-1-... GN 967-...-40-...-2-... GN 967-...-45-...-1-... GN 967-...-45-...-2-...	GN 968-8-M5-12-A GN 968-8-M5-12-B GN 968-8-M6-12-A GN 968-8-M6-12-B - - - -		GN 968-10-M5-14-A GN 968-10-M5-14-B GN 968-10-M6-14-A GN 968-10-M6-14-B GN 968-10-M8-16-A GN 968-10-M8-16-B GN 968-10-M8-16-A GN 968-10-M8-16-B	